



## **Phottix Indra360 TTL Studio Light**

Firmware Version v1.08

Change Log

December 28, 2015

1. Improves High Speed Sync (HSS) functions in TTL and M (Manual) modes for Nikon & Canon.
2. Improves TTL exposure.
3. Addition of a Color / Action option for M (Manual) mode to improve color temperature in Custom Settings Menu. To use: Hold the menu button, and, Press and rotate the control knob access the Custom Setting menu.  
"Color" mode offers more stable color temperatures of 5500K +/- 200K, but does not support HSS. "Action" mode supports HSS but color temperature variations of 5500K +/- 400K.
4. Deletes the Rotate Knob function at the top of the Menu page.
5. Improves Modeling Light Auto Off time to 25 minutes.
6. Improves recycle time

## **Phottix Indra360 TTL 影楼灯**

固件版本 V1.08

更改纪录

2015 年 12 月 28 日

1. 改善 TTL 及手动模式下佳能及尼康的高速同步功能
2. 改善 TTL 的准确度
3. 新增 Color 及 Action 模式来改善色温。使用方式：同时按选单选择键及旋钮键进入自定义功能选单。  
Color 模式：提供更稳定的色温 (5500K +/- 200K)，但不支持高速同步功能  
Action 模式：支持高速同步但色温范围在 (5500K +/- 400K)
4. 在主选单时，旋钮键取消功能
5. 造型灯自动熄灭时间改成 25 分钟
6. 改善回电速度